

## Slotted countersunk head screw DIN 963 A Steel Zinc plated 4.8 M2X30



Article number	24540.020.030
Brand	-
UBB	950353129667
UNSPSC	31161504
EAN	8715492632548
PKG. of 200	Full Box Only

### Technical Parameters

Diameter (d-D)	M2
Length (L) (mm)	30
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

### Standards

NF	E25-123
ASME	B18.6.7M
ISO	2009
BS	4183
DIN	963 A

### Technical Specification

Thread length (min.)	16
$d_k$ (max.)	3.8
Full thread if $L \leq$	18
$k$ (max.)	1.2
$n$	0.5
$P$	0.40
$t$ (min.)	0.4

### Technical Drawing

