



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M2,5X8

Article number	24540.025.008
Brand	-
UBB	950353335173
UNSPSC	31161504
EAN	8715492632623
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M2.5
Length	8 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NEN	≈2370
BS	≈4183
ASME	≈B18.6.7M
NF	≈E25-123
DIN	963
ISO	≈2009

Technical Specification

d-D	M2.5
Thread length (min.)	18
dk (max.)	4.7
Full thread if $L \leq$	20
k (max.)	1.5
L (mm)	8
n	0.6
P	0.45
t (min.)	0.5

Technical Drawing

