

Slotted countersunk head screw DIN 963 A Steel Zinc plated 4.8 M3X16



Article number	24540.030.016
Brand	-
UBB	950353131473
UNSPSC	31161504
EAN	8715492632883
PKG. of 200	Full Box Only

Technical Parameters

Diameter (d-D)	M3
Length (L) (mm)	16
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-123
DIN	963 A
ASME	B18.6.7M
ISO	2009
BS	4183

Technical Specification

Thread length (min.)	19
d_k (max.)	5.6
Full thread if $L \leq$	22
k (max.)	1.65
n	0.8
P	0.50
t (min.)	0.6

Technical Drawing

