



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M3X45

Article number	24540.030.045
Brand	-
UBB	950353132042
UNSPSC	31161504
EAN	8715492632975
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	45 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈2009
BS	≈4183
NEN	≈2370
ASME	≈B18.6.7M
DIN	963
NF	≈E25-123

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if $L \leq$	22
k (max.)	1.65
L (mm)	45
n	0.8
P	0.5
t (min.)	0.6

Technical Drawing

