



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M3X70

Article number	24540.030.070
Brand	-
UBB	500621767507
UNSPSC	31161504
EAN	8715494509084
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	70 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈2009
NF	≈E25-123
DIN	963
NEN	≈2370
ASME	≈B18.6.7M
BS	≈4183

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if $L \leq$	22
k (max.)	1.65
L (mm)	70
n	0.8
P	0.5
t (min.)	0.6

Technical Drawing

