

Slotted countersunk head screw DIN 963 A Steel Zinc plated 4.8 M3X100



Article No.	24540.030.100
Brand	-
UBB	950353132539
UNSPSC	31161504
EAN	8715492633033
PKG. of 200	Full Box Only

Technical Parameters

Diameter (d-D)	M3
Length (L) (mm)	100
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	B18.6.7M
NF	E25-123
BS	4183
ISO	2009
DIN	963 A

Technical Specification

d_k	5.6
Full thread if $L \leq$	22
k (max.)	1.65
n	0.8
P	0.50

Technical Drawing

