



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M3,5X8

Article number	24540.035.008
Brand	-
UBB	950353132794
UNSPSC	31161504
EAN	8715492633064
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3.5
Length	8 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-123
ASME	≈B18.6.7M
BS	≈4183
NEN	≈2370
ISO	≈2009
DIN	963

Technical Specification

d-D	M3.5
Thread length (min.)	20
dk (max.)	6.5
Full thread if $L \leq$	25
k (max.)	1.93
L (mm)	8
n	0.8
P	0.6
t (min.)	0.7

Technical Drawing

