



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M4X10

Article number	24540.040.010
Brand	-
UBB	950353133784
UNSPSC	31161504
EAN	8715492633194
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M4
Length	10 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
DIN	963
NEN	≈2370
BS	≈4183
NF	≈E25-123
ISO	≈2009

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
Full thread if $L \leq$	25
k (max.)	2.2
L (mm)	10
n	1
P	0.7
t (min.)	0.8

Technical Drawing

