



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M4X40

Article number	24540.040.040
Brand	-
UBB	950353134444
UNSPSC	31161504
EAN	8715492633293
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M4
Length	40 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	963
ISO	≈2009
NF	≈E25-123
BS	≈4183
ASME	≈B18.6.7M
NEN	≈2370

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
Full thread if $L \leq$	25
k (max.)	2.2
L (mm)	40
n	1
P	0.7
t (min.)	0.8

Technical Drawing

