



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M4X80

Article number	24540.040.080
Brand	-
UBB	950353134931
UNSPSC	31161504
EAN	8715492633347
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M4
Length	80 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈2009
NEN	≈2370
ASME	≈B18.6.7M
DIN	963
BS	≈4183
NF	≈E25-123

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
Full thread if $L \leq$	25
k (max.)	2.2
L (mm)	80
n	1
P	0.7
t (min.)	0.8

Technical Drawing

