



Slotted countersunk head screw DIN 963 A Steel Zinc plated 4.8 M4X100

Article number	24540.040.100
Brand	-
UBB	950353135011
UNSPSC	31161504
EAN	8715492633354
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M4
Length	100 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈2009
DIN	963
BS	≈4183
NEN	≈2370
NF	≈E25-123
ASME	≈B18.6.7M

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
Full thread if $L \leq$	25
k (max.)	2.2
L (mm)	100
n	1
P	0.7
t (min.)	0.8

Technical Drawing

