



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M5X10

Article number	24540.050.010
Brand	-
UBB	950353135359
UNSPSC	31161504
EAN	8715492633385
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	10 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈2009
ASME	≈B18.6.7M
NF	≈E25-123
NEN	≈2370
BS	≈4183
DIN	963

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if $L \leq$	30
k (max.)	2.5
L (mm)	10
n	1.2
P	0.8
t (min.)	1

Technical Drawing

