

Slotted countersunk head screw DIN 963 A Steel Zinc plated 4.8 M5X60



Article No. 24540.050.060

Brand -

UBB 950353136340

UNSPSC 31161504

EAN 8715492633521

PKG. of 200 Full Box Only

Technical Parameters

| | |
|-------------------|------------------|
| Diameter (d-D) | M5 |
| Length (L) (mm) | 60 |
| Class | 4.8 |
| Driving features | Slotted |
| Head shape | Countersunk head |
| Material | Steel |
| Surface treatment | Zinc plated |
| Thread | Metric thread |

Standards

| | |
|------|----------|
| DIN | 963 A |
| ISO | 2009 |
| ASME | B18.6.7M |
| NF | E25-123 |
| BS | 4183 |

Technical Specification

| | |
|-------------------------|------|
| d_k | 9.2 |
| Full thread if $L \leq$ | 30 |
| k (max.) | 2.5 |
| n | 1.2 |
| P | 0.80 |

Technical Drawing

