



**Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M5X80**

|                |               |
|----------------|---------------|
| Article number | 24540.050.080 |
| Brand          | -             |
| UBB            | 950353136597  |
| UNSPSC         | 31161504      |
| EAN            | 8715492633552 |
| PKG. of 100    | Full Box Only |

**Technical Parameters**

|                   |                  |
|-------------------|------------------|
| Diameter          | M5               |
| Length            | 80 mm            |
| Class             | 4.8              |
| Driving features  | Slotted          |
| Head shape        | Countersunk head |
| Material          | Steel            |
| Surface treatment | Zinc plated      |
| Thread            | Metric thread    |

**Standards**

|      |           |
|------|-----------|
| DIN  | 963       |
| NEN  | ≈2370     |
| ISO  | ≈2009     |
| NF   | ≈E25-123  |
| BS   | ≈4183     |
| ASME | ≈B18.6.7M |

**Technical Specification**

|                         |     |
|-------------------------|-----|
| d-D                     | M5  |
| Thread length (min.)    | 25  |
| dk (max.)               | 9.2 |
| Full thread if $L \leq$ | 30  |
| k (max.)                | 2.5 |
| L (mm)                  | 80  |
| n                       | 1.2 |
| P                       | 0.8 |
| t (min.)                | 1   |

**Technical Drawing**

