



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M5X100

Article number	24540.050.100
Brand	-
UBB	950353136670
UNSPSC	31161504
EAN	8715492633576
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M5
Length	100 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-123
DIN	963
BS	≈4183
ASME	≈B18.6.7M
NEN	≈2370
ISO	≈2009

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if $L \leq$	30
k (max.)	2.5
L (mm)	100
n	1.2
P	0.8
t (min.)	1

Technical Drawing

