



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M6X8

Article number	24540.060.008
Brand	-
UBB	950353136753
UNSPSC	31161504
EAN	8715492633583
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	8 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈2009
BS	≈4183
ASME	≈B18.6.7M
DIN	963
NEN	≈2370
NF	≈E25-123

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
Full thread if $L \leq$	35
k (max.)	3
L (mm)	8
n	1.6
P	1
t (min.)	1.2

Technical Drawing

