



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M6X18

Article number	24540.060.018
Brand	-
UBB	950353509900
UNSPSC	31161504
EAN	8715492633637
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	18 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	963
NF	≈E25-123
ASME	≈B18.6.7M
ISO	≈2009
NEN	≈2370
BS	≈4183

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
Full thread if $L \leq$	35
k (max.)	3
L (mm)	18
n	1.6
P	1
t (min.)	1.2

Technical Drawing

