

Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M6X20



Article number	24540.060.020
Brand	-
UBB	950353137173
UNSPSC	31161504
EAN	8715492633644
PKG. of 200	Full Box Only

Technical Parameters

Diameter (d-D)	M6
Length (L) (mm)	20
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	963
NF	≈E25-123
BS	≈4183
ISO	≈2009
ASME	≈B18.6.7M

Technical Specification

Thread length (min.)	28
d_k (max.)	11
Full thread if $L \leq$	35
k (max.)	3
n	1.6
P	1
t (min.)	1.2

Technical Drawing

