



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M6X30

Article number	24540.060.030
Brand	-
UBB	950353137330
UNSPSC	31161504
EAN	8715492633675
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	30 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NEN	≈2370
ISO	≈2009
DIN	963
ASME	≈B18.6.7M
NF	≈E25-123
BS	≈4183

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
Full thread if $L \leq$	35
k (max.)	3
L (mm)	30
n	1.6
P	1
t (min.)	1.2

Technical Drawing

