



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M6X40

Article number	24540.060.040
Brand	-
UBB	950353137587
UNSPSC	31161504
EAN	8715492633699
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	40 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-123
NEN	≈2370
DIN	963
ASME	≈B18.6.7M
BS	≈4183
ISO	≈2009

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
Full thread if $L \leq$	35
k (max.)	3
L (mm)	40
n	1.6
P	1
t (min.)	1.2

Technical Drawing

