



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M6X55

Article number	24540.060.055
Brand	-
UBB	950353891969
UNSPSC	31161504
EAN	8715492633729
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M6
Length	55 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NEN	≈2370
ASME	≈B18.6.7M
NF	≈E25-123
BS	≈4183
ISO	≈2009
DIN	963

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
Full thread if $L \leq$	35
k (max.)	3
L (mm)	55
n	1.6
P	1
t (min.)	1.2

Technical Drawing

