



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M6X60

Article number	24540.060.060
Brand	-
UBB	950353137827
UNSPSC	31161504
EAN	8715492633736
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	60 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	963
BS	≈4183
ASME	≈B18.6.7M
ISO	≈2009
NEN	≈2370
NF	≈E25-123

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
Full thread if $L \leq$	35
k (max.)	3
L (mm)	60
n	1.6
P	1
t (min.)	1.2

Technical Drawing

