



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M8X25

Article number	24540.080.025
Brand	-
UBB	950353138650
UNSPSC	31161504
EAN	8715492633873
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	25 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
DIN	963
BS	≈4183
ISO	≈2009
NEN	≈2370
NF	≈E25-123

Technical Specification

d-D	M8
Thread length (min.)	34
dk (max.)	14.5
Full thread if $L \leq$	40
k (max.)	4
L (mm)	25
n	2
P	1.25
t (min.)	1.6

Technical Drawing

