



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M8X80

Article number	24540.080.080
Brand	-
UBB	950353139492
UNSPSC	31161504
EAN	8715492633972
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	80 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈2009
BS	≈4183
NEN	≈2370
DIN	963
ASME	≈B18.6.7M
NF	≈E25-123

Technical Specification

d-D	M8
Thread length (min.)	34
dk (max.)	14.5
Full thread if $L \leq$	40
k (max.)	4
L (mm)	80
n	2
P	1.25
t (min.)	1.6

Technical Drawing

