



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M8X90

Article number	24540.080.090
Brand	-
UBB	500621767689
UNSPSC	31161504
EAN	8715494509091
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	90 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	963
NF	≈E25-123
BS	≈4183
ISO	≈2009
NEN	≈2370
ASME	≈B18.6.7M

Technical Specification

d-D	M8
Thread length (min.)	34
dk (max.)	14.5
Full thread if $L \leq$	40
k (max.)	4
L (mm)	90
n	2
P	1.25
t (min.)	1.6

Technical Drawing

