



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M10X16

Article number	24540.100.016
Brand	-
UBB	950353139641
UNSPSC	31161504
EAN	8715492634016
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M10
Length	16 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

BS	≈4183
NEN	≈2370
NF	≈E25-123
ASME	≈B18.6.7M
DIN	963
ISO	≈2009

Technical Specification

d-D	M10
Thread length (min.)	40
dk (max.)	18
Full thread if $L \leq$	50
k (max.)	5
L (mm)	16
n	2.5
P	1.5
t (min.)	2

Technical Drawing

