



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M10X30

Article number	24540.100.030
Brand	-
UBB	950353139989
UNSPSC	31161504
EAN	8715492634047
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M10
Length	30 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

BS	≈4183
NF	≈E25-123
DIN	963
NEN	≈2370
ASME	≈B18.6.7M
ISO	≈2009

Technical Specification

d-D	M10
Thread length (min.)	40
dk (max.)	18
Full thread if $L \leq$	50
k (max.)	5
L (mm)	30
n	2.5
P	1.5
t (min.)	2

Technical Drawing

