



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M10X40

Article number	24540.100.040
Brand	-
UBB	950353140128
UNSPSC	31161504
EAN	8715492634061
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	40 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
DIN	963
ISO	≈2009
BS	≈4183
NEN	≈2370
NF	≈E25-123

Technical Specification

d-D	M10
Thread length (min.)	40
dk (max.)	18
Full thread if $L \leq$	50
k (max.)	5
L (mm)	40
n	2.5
P	1.5
t (min.)	2

Technical Drawing

