

## Slotted countersunk head screw DIN 963 A Steel Zinc plated 4.8 M10X60



Article No.	24540.100.060
Brand	-
UBB	950353140383
UNSPSC	31161504
EAN	8715492634108
PKG. of 100	Full Box Only

### Technical Parameters

Diameter (d-D)	M10
Length (L) (mm)	60
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

### Standards

NF	E25-123
DIN	963 A
BS	4183
ASME	B18.6.7M
ISO	2009

### Technical Specification

$d_k$	18
Full thread if $L \leq$	50
k (max.)	5
n	2.5
P	1.50

### Technical Drawing

