



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M12X60

Article number	24540.120.060
Brand	-
UBB	950353141373
UNSPSC	31161504
EAN	8715492634221
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Length	60 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NEN	≈2370
ISO	≈2009
DIN	963
BS	≈4183
ASME	≈B18.6.7M
NF	≈E25-123

Technical Specification

d-D	M12
Thread length (min.)	46
dk (max.)	22
Full thread if $L \leq$	60
k (max.)	6
L (mm)	60
n	3
P	1.75
t (min.)	2.4

Technical Drawing

