



Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M16X50

Article number	24540.160.050
Brand	-
UBB	950353142108
UNSPSC	31161504
EAN	8715492634344
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M16
Length	50 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NEN	≈2370
DIN	963
ISO	≈2009
BS	≈4183
ASME	≈B18.6.7M
NF	≈E25-123

Technical Specification

d-D	M16
Thread length (min.)	58
dk (max.)	29
Full thread if $L \leq$	70
k (max.)	8
L (mm)	50
n	5
P	2
t (min.)	3.2

Technical Drawing

