



**Slotted countersunk head screw DIN 963 Steel Zinc plated 4.8 M20X50**

|                |               |
|----------------|---------------|
| Article number | 24540.200.050 |
| Brand          | -             |
| UBB            | 950353142850  |
| UNSPSC         | 31161504      |
| EAN            | 8715492634412 |
| PKG. of 50     | Full Box Only |

**Technical Parameters**

|                   |                  |
|-------------------|------------------|
| Diameter          | M20              |
| Length            | 50 mm            |
| Class             | 4.8              |
| Driving features  | Slotted          |
| Head shape        | Countersunk head |
| Material          | Steel            |
| Surface treatment | Zinc plated      |
| Thread            | Metric thread    |

**Standards**

|      |           |
|------|-----------|
| DIN  | 963       |
| NF   | ≈E25-123  |
| BS   | ≈4183     |
| ISO  | ≈2009     |
| NEN  | ≈2370     |
| ASME | ≈B18.6.7M |

**Technical Specification**

|                         |     |
|-------------------------|-----|
| d-D                     | M20 |
| Thread length (min.)    | 70  |
| dk (max.)               | 36  |
| Full thread if $L \leq$ | 80  |
| k (max.)                | 10  |
| L (mm)                  | 50  |
| n                       | 5   |
| P                       | 2.5 |
| t (min.)                | 4   |

**Technical Drawing**

