



Slotted countersunk head screw DIN 963 Steel Zinc plated yellow passivated 4.8 M3X8

Article number	24560.030.008
Brand	-
UBB	950353143684
UNSPSC	31161504
EAN	8715492634603
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	8 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
NF	≈E25-123
BS	≈4183
DIN	963
ISO	≈2009
NEN	≈2370

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if $L \leq$	22
k (max.)	1.65
L (mm)	8
n	0.8
P	0.5
t (min.)	0.6

Technical Drawing

