

## Slotted countersunk head screw DIN 963 Steel Zinc plated yellow passivated 4.8 M3X10



Article number	24560.030.010
Brand	-
UBB	950353143767
UNSPSC	31161504
EAN	8715492634627
PKG. of 500	Full Box Only

### Technical Parameters

Diameter (d-D)	M3
Length (L) (mm)	10
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

### Standards

ASME	≈B18.6.7M
NF	≈E25-123
BS	≈4183
ISO	≈2009
DIN	963

### Technical Specification

Thread length (min.)	19
$d_k$ (max.)	5.6
Full thread if $L \leq$	22
$k$ (max.)	1.65
$n$	0.8
$P$	0.50
$t$ (min.)	0.6

### Technical Drawing

