

## Slotted countersunk head screw DIN 963 A Steel Zinc plated yellow passivated 4.8 M3X16



Article No.	24560.030.016
Brand	-
UBB	950353143924
UNSPSC	31161504
EAN	8715492634641
PKG. of 500	Full Box Only

### Technical Parameters

Diameter (d-D)	M3
Length (L) (mm)	16
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

### Standards

DIN	963 A
BS	4183
ISO	2009
NF	E25-123
ASME	B18.6.7M

### Technical Specification

$d_k$	5.6
Full thread if $L \leq$	22
k (max.)	1.65
n	0.8
P	0.50

### Technical Drawing

