



Slotted countersunk head screw DIN 963 Steel Zinc plated yellow passivated 4.8 M3X20

Article number	24560.030.020
Brand	-
UBB	950353144005
UNSPSC	31161504
EAN	8715492634665
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	20 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

NF	≈E25-123
ASME	≈B18.6.7M
NEN	≈2370
ISO	≈2009
DIN	963
BS	≈4183

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if $L \leq$	22
k (max.)	1.65
L (mm)	20
n	0.8
P	0.5
t (min.)	0.6

Technical Drawing

