

Slotted countersunk head screw DIN 963 Steel Zinc plated yellow passivated 4.8 M3X50



Article number	24560.030.050
Brand	-
UBB	950353766989
UNSPSC	31161504
EAN	8715492634719
PKG. of 500	Full Box Only

Technical Parameters

Diameter (d-D)	M3
Length (L) (mm)	50
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

DIN	963
NF	≈E25-123
ISO	≈2009
BS	≈4183
ASME	≈B18.6.7M

Technical Specification

Thread length (min.)	19
d_k (max.)	5.6
Full thread if $L \leq$	22
k (max.)	1.65
n	0.8
P	0.50
t (min.)	0.6

Technical Drawing

