

Slotted countersunk head screw DIN 963 A Steel Zinc plated yellow passivated 4.8 M3X60



Article number	24560.030.060
Brand	-
UBB	951353498011
UNSPSC	31161504
EAN	8715492634726
PKG. of 500	Full Box Only

Technical Parameters

Diameter (d-D)	M3
Length (L) (mm)	60
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

BS	4183
ISO	2009
DIN	963 A
ASME	B18.6.7M
NF	E25-123

Technical Specification

Thread length (min.)	19
d_k (max.)	5.6
Full thread if $L \leq$	22
k (max.)	1.65
n	0.8
P	0.50
t (min.)	0.6

Technical Drawing

