



Slotted countersunk head screw DIN 963 Steel Zinc plated yellow passivated 4.8 M4X8

Article number	24560.040.008
Brand	-
UBB	950353144344
UNSPSC	31161504
EAN	8715492634771
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	8 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

BS	≈4183
NF	≈E25-123
DIN	963
ISO	≈2009
ASME	≈B18.6.7M
NEN	≈2370

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
Full thread if $L \leq$	25
k (max.)	2.2
L (mm)	8
n	1
P	0.7
t (min.)	0.8

Technical Drawing

