



Slotted countersunk head screw DIN 963 Steel Zinc plated yellow passivated 4.8 M4X40

Article number	24560.040.040
Brand	-
UBB	950353145093
UNSPSC	31161504
EAN	8715492634856
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	40 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

DIN	963
ISO	≈2009
ASME	≈B18.6.7M
NF	≈E25-123
BS	≈4183
NEN	≈2370

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
Full thread if $L \leq$	25
k (max.)	2.2
L (mm)	40
n	1
P	0.7
t (min.)	0.8

Technical Drawing

