



Slotted countersunk head screw DIN 963 Steel Zinc plated yellow passivated 4.8 M4X50

Article number	24560.040.050
Brand	-
UBB	951353498193
UNSPSC	31161504
EAN	8715492634863
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	50 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

NEN	≈2370
NF	≈E25-123
DIN	963
BS	≈4183
ISO	≈2009
ASME	≈B18.6.7M

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
Full thread if $L \leq$	25
k (max.)	2.2
L (mm)	50
n	1
P	0.7
t (min.)	0.8

Technical Drawing

