



Slotted countersunk head screw DIN 963 Steel Zinc plated yellow passivated 4.8 M4X60

Article number	24560.040.060
Brand	-
UBB	950353767557
UNSPSC	31161504
EAN	8715492634870
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	60 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

BS	≈4183
ASME	≈B18.6.7M
ISO	≈2009
NEN	≈2370
NF	≈E25-123
DIN	963

Technical Specification

d-D	M4
Thread length (min.)	22
dk (max.)	7.5
Full thread if $L \leq$	25
k (max.)	2.2
L (mm)	60
n	1
P	0.7
t (min.)	0.8

Technical Drawing

