

## Slotted countersunk head screw DIN 963 A Steel Zinc plated yellow passivated 4.8 M5X25



Article No.	24560.050.025
Brand	-
UBB	950353145580
UNSPSC	31161504
EAN	8715492634931
PKG. of 500	Full Box Only

### Technical Parameters

Diameter (d-D)	M5
Length (L) (mm)	25
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

### Standards

ASME	B18.6.7M
DIN	963 A
NF	E25-123
BS	4183
ISO	2009

### Technical Specification

$d_k$	9.2
Full thread if $L \leq$	30
k (max.)	2.5
n	1.2
P	0.80

### Technical Drawing

