

Slotted countersunk head screw DIN 963 Steel Zinc plated yellow passivated 4.8 M6X20



Article number 24560.060.020

Brand -

UBB 950353146166

UNSPSC 31161504

EAN 8715492635037

PKG. of 200 Full Box Only

Technical Parameters

Diameter (d-D)	M6
Length (L) (mm)	20
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

BS	≈4183
DIN	963
ISO	≈2009
NF	≈E25-123
ASME	≈B18.6.7M

Technical Specification

Thread length (min.)	28
d_k (max.)	11
Full thread if $L \leq$	35
k (max.)	3
n	1.6
P	1
t (min.)	1.2

Technical Drawing

