



Slotted countersunk head screw DIN 963 Steel Zinc plated yellow passivated 4.8 M6X25

Article number	24560.060.025
Brand	-
UBB	950353146240
UNSPSC	31161504
EAN	8715492635044
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	25 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

NEN	≈2370
BS	≈4183
NF	≈E25-123
ASME	≈B18.6.7M
DIN	963
ISO	≈2009

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
Full thread if $L \leq$	35
k (max.)	3
L (mm)	25
n	1.6
P	1
t (min.)	1.2

Technical Drawing

