



Slotted countersunk head screw DIN 963 Steel Zinc plated yellow passivated 4.8 M6X40

Article number	24560.060.040
Brand	-
UBB	950353146406
UNSPSC	31161504
EAN	8715492635075
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	40 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

ASME	≈B18.6.7M
BS	≈4183
ISO	≈2009
NEN	≈2370
NF	≈E25-123
DIN	963

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
Full thread if $L \leq$	35
k (max.)	3
L (mm)	40
n	1.6
P	1
t (min.)	1.2

Technical Drawing

