



Slotted countersunk head screw DIN 963 Steel Zinc plated yellow passivated 4.8 M6X70

Article number	24560.060.070
Brand	-
UBB	951353498508
UNSPSC	31161504
EAN	8715492635105
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	70 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

BS	≈4183
NEN	≈2370
DIN	963
ISO	≈2009
NF	≈E25-123
ASME	≈B18.6.7M

Technical Specification

d-D	M6
Thread length (min.)	28
dk (max.)	11
Full thread if $L \leq$	35
k (max.)	3
L (mm)	70
n	1.6
P	1
t (min.)	1.2

Technical Drawing

