



Slotted countersunk head screw DIN 963 Steel Zinc plated yellow passivated 4.8 M8X30

Article number	24560.080.030
Brand	-
UBB	950353146992
UNSPSC	31161504
EAN	8715492635150
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	30 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

DIN	963
BS	≈4183
ASME	≈B18.6.7M
NF	≈E25-123
NEN	≈2370
ISO	≈2009

Technical Specification

d-D	M8
Thread length (min.)	34
dk (max.)	14.5
Full thread if $L \leq$	40
k (max.)	4
L (mm)	30
n	2
P	1.25
t (min.)	1.6

Technical Drawing

