



Slotted countersunk head screw DIN 963 Steel Zinc plated black passivated 4.8 M2X6

Article number	24565.020.006
Brand	-
UBB	950353621101
UNSPSC	31161504
EAN	8715492635242
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M2
Length	6 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated black passivated
Thread	Metric thread

Standards

BS	≈4183
DIN	963
ISO	≈2009
ASME	≈B18.6.7M
NF	≈E25-123
NEN	≈2370

Technical Specification

d-D	M2
Thread length (min.)	16
dk (max.)	3.8
Full thread if $L \leq$	18
k (max.)	1.2
L (mm)	6
n	0.5
P	0.4
t (min.)	0.4

Technical Drawing

