



Slotted countersunk head screw DIN 963 Steel Zinc plated black passivated 4.8 M3X10

Article number	24565.030.010
Brand	-
UBB	950353621366
UNSPSC	31161504
EAN	8715492635273
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M3
Length	10 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated black passivated
Thread	Metric thread

Standards

NEN	≈2370
BS	≈4183
ISO	≈2009
ASME	≈B18.6.7M
DIN	963
NF	≈E25-123

Technical Specification

d-D	M3
Thread length (min.)	19
dk (max.)	5.6
Full thread if $L \leq$	22
k (max.)	1.65
L (mm)	10
n	0.8
P	0.5
t (min.)	0.6

Technical Drawing

